



Pass and Seymour
Pin & Sleeve Watertight 20A Metal Back Box
Part No. PSBB201W

Double-Pole, 3-Wire, Angled Metallic Receptacle Box. 20A. 1/2-inch Hub.



Features & Benefits

Legrand Pin & Sleeve products provide installation ease, enduring performance in harsh conditions, and guaranteed IEC 309 compatibility.

Nylon construction for high impact and corrosion resistance.

Locking ring with an integral neoprene gasket provides watertight seal when plug and connector/receptacle are mated.

Combination-head screws for added convenience and quick installation.

Cover with integral neoprene gasket provides watertight seal.

Arrives ready to wire, with cord grip open and cable-ready. Terminal screws come backed out and ready to wire. Front and back body require no disassembly prior to assembly.

Nickel-plated brass pins provide extracorrosion resistance without sacrificing electrical conductivity.

Natural-rubber grommets provide watertight protection at cable entry.

Revolutionary, hinged cord grip for durable performance and ease of installation.

Specifications

General Info

Product Line	Pass & Seymour	Country Of Origin	United States
Application Sector	Commercial	Standard	UL Listed

Dimensions

Product Width US	2.75 in	Product Depth US	3.17 in
Product Height US	5.6 in		

Technical Information

Number of Wires	3	Amperage	20 A
Number of Poles	Double Pole	Wire Size	2 AWG
Voltage	277.0 V		
