

Pass and Seymour PlugTail® Switch Right Angle Connector 4-Wire, 6-in Solid THHN12 Part No. PTS6SOL4

PlugTail® Switch Right Angle Connector 4-Wire, 6-inch Solid THHN12

Features & Benefits

All PlugTail: Connectors are available in any wire length up to 25 inches

Ultrasonically welded polycarbonate connector housing secures terminations and conductors in a UL Listed, finger safe housing. Audible snapping latch assures connection, allows release.

For covering patents, see www.legrand.us/patents.

Large crimped and welded brass contacts

Pre-stripped connector leads fasten to conductors, easier than standard pigtails.

For compatible wall plate options, from our TradeMaster unbreakable plates to our radiant screwless plates to our metal wall plates, click here.

Specifications

General Info

Product Line	Pass & Seymour	Country Of Origin	Mexico
Application Sector	Commercial	Standard	UL 20
Listing Agencies / 3rd	d Party Agencies		
cULus Listed	Yes		
Technical Information	1		
Contact Rating	120/277Vac	Number of Poles	3-Way
Wattage	3 W	Voltage	120.0 V