



Pass and Seymour  
**PlugTail® Hospital-Grade 15A USB Charging Receptacles, Black**  
 Part No. PTTR15HACUSBBK



PlugTail® Hospital Grade USB Charging Receptacles provide the convenience of mobile charging without the need for a bulky AC adapter. This device is a perfect match for the constant needs of today's mobile environment and is rugged enough to withstand hard-use commercial applications. It comes equipped with two UL Fed Spec AC receptacles and two USB charging ports for mobile devices: one Type-A port and one Type-C port for newer products. An efficient, 15.5W power supply provides the power needed for charging mobile phones and tablets. The PlugTail® termination provides a more productive, secure, and safer installation and allows you to connect with the future of wiring device innovations. For detailed PlugTail® information, visit our PlugTail® Headquarters.

## Features & Benefits

- AC receptacles are tamper resistant as standard : patented shutter system prevents improper insertion of foreign objects
- Efficient, 15.5W power supply for fast charging of mobile phones and tablets
- Triple-wipe, brass line contacts for 15A commercial applications
- Multiple color options available
- Zinc-plated steel for corrosion resistance
- 5Vdc Type-C USB port to charge USB Type-C compatible mobile devices
- PlugTail termination allows for more productive, finger-safe installation and added future flexibility
- Stainless steel auto-ground clips assure positive ground
- Available in 15 & 20A, Specification Grade and Hospital Grade configurations

## Specifications

### General Info

|                   |                |       |       |
|-------------------|----------------|-------|-------|
| Product Line      | Pass & Seymour | Color | Black |
| Country Of Origin | China          |       |       |

### Dimensions

|                   |          |                  |         |
|-------------------|----------|------------------|---------|
| Product Width US  | 1.693 in | Product Depth US | 1.45 in |
| Product Height US | 2.677 in |                  |         |

### Listing Agencies / 3rd Party Agencies

|              |     |
|--------------|-----|
| cULus Listed | Yes |
|--------------|-----|

---

## Technical Information

---

|                  |       |                |      |
|------------------|-------|----------------|------|
| USB Amperage     | 3.1 A | Number of USBs | 2    |
| USB Power Output | 15 W  | Amperage       | 15 A |

---