



radiant Collection
radiant® 15A Tamper-Resistant USB Type A/C Outlet, Black
Part No. R26USBACBK



Make it easier to get a full battery for your smartphones, tablets and more with the convenience of built-in charging. A perfect charging solution for your current and future electronic devices, this tamper-resistant USB outlet features connections for USB Type-A and the newer USB Type-C. Easily replacing traditional outlets in as little as ten minutes, this outlet offers accessible charging without needing bulky adapters or sacrificing your plugs, and features the sleek, clean lines of radiant® for a sophisticated look. Made exclusively for use with screwless Wall Plates from the radiant® Collection, sold separately.

Features & Benefits

- Provides convenient built-in charging, without sacrificing plugs or requiring a bulky adapter.
- Accommodates all mobile devices with connections for both traditional USB Type-A and the newer USB Type-C, which features a smaller, reversible connector and high-speed specs.
- All Legrand USB Outlets are manufactured through high-quality design, sourcing and production, and backed by a Lifetime Warranty.
- Protects children with a patented tamper-resistant shutter system that prevents improper insertion of foreign objects, complete with "invisi-shutters" for an invisible effect.
- Replaces a traditional outlet easily, in as little as 10 minutes.
- More color options available to fit any style, including finishes to match current hardware and lighting trends.
- Complete the look with a sleek, screwless radiant® Wall Plate, and coordinate with other designer switches and outlets available from the radiant® Collection.

Specifications

General Info

| | | | |
|-------------------|--------------------------------|-------------------------|---|
| Product Line | Pass & Seymour | Replaced by Part Number | |
| Color | Black | Finish | Matte |
| Country Of Origin | China | Number of Receptacles | 2 |
| Features | USB-A Charging, USB-C Charging | Outlet Type | Indoor, Residential, Tamper-Resistant, USB-Charging |
| Warranty Type | 1-Year Limited Warranty | Type | Outlet |

Dimensions

| | | | |
|-------------------|----------|------------------|---------|
| Product Width US | 1.693 in | Product Depth US | 1.35 in |
| Product Height US | 4.18 in | | |

Listing Agencies / 3rd Party Agencies

| | |
|--------------|-----|
| cULus Listed | Yes |
|--------------|-----|

Additional Information

| | |
|-------------------------------|-----|
| Product Environmental Profile | Yes |
|-------------------------------|-----|

Technical Information

| | | | |
|--------------------------|---|-------------------------|-------------|
| Is Tamper-Resistant | Yes | USB Amperage | 3.1 A |
| Number of USBs | 2 | USB Power Output | 15 W |
| Amperage | 15 A | Number of Poles | Double Pole |
| Indoor/Outdoor | Indoor | NEMA Configuration Code | 5-15R |
| Mounting Type | Box | Voltage | 125.0 V |
| Environmental Conditions | 95% (relative humidity, non-condensing) | | |
