



radiant Collection

radiant® 15A Tamper Resistant Ultra Fast PLUS Power Delivery USB Type C/C Outlet, Nickel

Part No. R26USBPDNICC6



Charge devices up to 2X faster with the Ultra-Fast PLUS Power Delivery USB Outlet. Made to deliver a leading 30 Watts of power and featuring two built-in Type-C USB connections, this solution adds advanced Power Delivery to the industry-leading amperage of our Ultra-Fast line. The result is a faster, future-proof option for convenient in-wall charging, specially designed to optimize performance for your Power Delivery-enabled devices. Easily replace a traditional outlet in as little as ten minutes to gain the modern functionality of intelligent charging for maximized speeds, complete with multi-layered overcurrent protection to keep the outlet and your devices safe from damage. Made exclusively for use with screwless Wall Plates from the radiant® Collection, sold separately.

Features & Benefits

Charge the latest devices up to 2X as fast, thanks to the industry-leading 6.0A of our Ultra-Fast line and a whopping 30W of power courtesy of advanced Power Delivery

Built for intelligent charging, the outlet detects and delivers the precise amount of power needed to maximize charging speeds

Provides fast and convenient built-in charging through two future-proof USB Type-C ports, accommodating new and upcoming devices without an adapter

Helpful indicator light lets you see charging status at a glance. Light glows yellow while charging is in progress, and shows green once the device battery is sufficiently charged

Includes multiple layers of overcurrent protection, ensuring the outlet and your favorite devices can charge at optimal levels without risk of damage

All Legrand USB Outlets are manufactured through high-quality design, sourcing and production, and backed by a Lifetime Warranty

Protects children with a patented tamper-resistant shutter system that prevents improper insertion of foreign objects, complete with "invisi-shutters" for an invisible effect

Replaces a traditional outlet easily, in as little as 10 minutes, with features like scalloped cover design and posted side-wire terminal screws for faster installation

More color options available to fit any style, including finishes to match current hardware and lighting trends

Specifications

General Info

Product Line

Pass & Seymour

Replaced by Part Number

Color

Nickel

Finish

Nickel

Country Of Origin

China

Features

USB-C Charging

Outlet Type

USB-Charging

Application Sector

Residential/Commercial

Type

Tamper-Resistant, USB

Dimensions

Product Width US	1.693 in	Product Depth US	1.35 in
------------------	----------	------------------	---------

Product Height US	4.18 in
-------------------	---------

Additional Information

RoHS Conformant	Yes
-----------------	-----

Technical Information

USB Amperage	6 A	Connection	USB Type C/C
--------------	-----	------------	--------------

Number of USBs	2	Output Current	6A
----------------	---	----------------	----

USB Power Output	30 W	Amperage	15 A
------------------	------	----------	------

Current Rating	15 A	Indoor/Outdoor	Indoor
----------------	------	----------------	--------

Mounting Type	Box	Voltage	125.0 V
---------------	-----	---------	---------
