




radiant Collection  
**radiant® Single Pole/3-Way Fan Speed Control, Tri-Color**  
Part No. RHDH163PTCCCV6



Upgrade your fan control with the sweet sound of silence. Specially designed to virtually eliminate the fan motor "hum." This device provides quieter fan speed control while featuring the sleek, clean lines of radiant® for a sophisticated touch. This fan control switch handles a max load of 1.6A. Made exclusively for use with screwless Wall Plates from the radiant® Collection, sold separately.

## Features & Benefits

Designed to virtually eliminate the motor's hum for quieter use.

Offers installation flexibility, working in both single-pole and 3-way applications.

Locator light illuminates when switch is off, emitting a soft glow to help you find it in the dark.

Complete the look with a sleek, screwless radiant® Wall Plate, and coordinate with other designer switches and outlets available from the radiant® Collection.

Installs easily in place of a standard light or fan control switch. Rated for a max load of 1.6A.

Returns the fan to its previous level after a power failure.

More color options available to fit any style.

## Specifications

### General Info

Product Line	Pass & Seymour	Color	Ivory, Light Almond, White
Country Of Origin	China	Features	Fan Control
Switch Type	Paddle	Number of Switches	1
Warranty Type	Limited Lifetime Warranty		

### Dimensions

Product Width US	1.75 in	Product Depth US	1.25 in
Product Height US	4.25 in		

---

## Listing Agencies / 3rd Party Agencies

---

cULus Listed                      Yes

---

## Technical Information

---

Number of Gangs	1	Amperage	15 A
-----------------	---	----------	------

---

Number of Poles	3-Way, Single Pole	Mounting Type	Box
-----------------	--------------------	---------------	-----

---

Voltage	120.0 V
---------	---------

---