

radiant Collection radiant® 120V, 700VA, Magnetic Low-Voltage Single Pole/3-Way Dimmer, Tri-Color Part No. RHLV703PTC



Upgrade your space with precise dimming control and exceptional style, while saving energy and extending bulb life by reducing the amount of electricity required to power the lights. Made exclusively for use with screwless Wall Plates from the radiant® Collection, sold separately.

Features & Benefits

Low-profile paddle switch offers smoother On/Off control, while a separate, ergonomic slider allows you to adjust light levels with precision	Usable in both single-pole and 3-way applications.
Locator light illuminates when switch is off, emitting a soft glow to help you find it in the dark.	Constant memory features returns lights to their previous level after a power failure or outage.
Features durable, high-impact resistant thermoplastic construction.	More color options available to fit any style, including finishes to match current hardware and lighting trends.
Complete the look with a sleek, screwless radiant® Wall Plate, and coordinate with other designer switches and outlets available from the radiant® Collection.	
Specifications	

General Info

Product Line	Pass & Seymour	Color	lvory, Light Almond, White
Country Of Origin	China	Switch Type	Paddle
Number of Switches	1	Application Sector	Residential
Standard	CSA Listed, cULus, UL Listed	Warranty Type	Limited Lifetime Warranty
Туре	Dimmer		
Dimensions			
Product Width US	1.75 in	Product Depth US	1.25 in

Product Height US	4.25 in				
Listing Agencies / 3rd Party Agencies					
cULus Listed	Yes				
Technical Information					
Frequency Rating	120VAC 60 Hz	Connection	Screw Terminals		
Number of Gangs	1	Amperage	15 A		
Bulb Compatibility	Halogen	Number of Poles	3-Way, Single Pole		
Wattage	700 W	Mounting Type	Box		
Voltage	120.0 V	Load	Low Voltage		
Environmental Conditions	Humidity: Less than 95% non condensing				