



Ceiling Fan Box with two captive mounting nails. Standard Grade. Four Auto/Clamps. 30 pack.

## Features & Benefits

Constructed of impact-resistant Noryl thermoplastic, making it virtually unbreakable and non-conductive.

UL Listed for fan and fixture support.

Depth-mounting gauge at bottom of bracket helps you align the box at the proper depth relative to the ceiling.

Dual mounting accepts fans or fixtures with 2.75 inch or 3.5 inch straps.

Phillips-head screws (#10-32 x 3 inch) mount the fan or fixture directly to the metal bracket.

For covering patents, see [www.legrand.us/patents](http://www.legrand.us/patents).

Auto Clamp cable clamps molded in, hold wire securely in box.

Large, 20.25 cubic inch capacity for extra wiring space.

Angled, rugged, metal mounting bracket safely and securely fastens fans or fixtures to the building structure.

Fan mounts directly to bracket through box with #10-32 screws (provided).

Ringed nails for tighter grip.

## Specifications

### General Info

Product Line	Pass & Seymour	Country Of Origin	United States
Standard	Residential/Commercial		

### Dimensions

Cubic Capacity	20.25 cu in
----------------	-------------

### Additional Information

Product Environmental Profile	Yes
-------------------------------	-----

---

## Technical Information

---

Number of Outlets	1
-------------------	---

---