



Pass and Seymour
Communication Plate, Two Gang, Ivory
Part No. SP211



Double gang, Double telephone or cable outlet 13/32-inch hole. Box mounted. Smooth Thermoset. .

Features & Benefits

Molded of rugged, practically indestructible self-extinguishing nylon. ('TP' series only.)

Available in Ivory, White, Brown, Gray, Black, Blue, Orange, Red, and Light Almond.

Nominal thickness, .070 inch.

Available in 'TP' series, extra 3/16 inch width and height than Standard size plates: and 'TPJ' series, extra 3/16 inch width and height than Junior-Jumbo size plates.

Preferred for hospital, industrial, institutional, and other high-abuse applications.

Specifications

General Info

Product Line	Pass & Seymour	Color	Ivory
Country Of Origin	Mexico	Wall Plate Type	Coaxial
Application Sector	Residential/Commercial	Standard	CSA, UL514

Dimensions

Product Width US	4.56 in	Product Depth US	0.2 in
Product Height US	4.5 in		

Listing Agencies / 3rd Party Agencies

CSA Listed	Yes	CSA File Number	17695
------------	-----	-----------------	-------

Technical Information

Cutout	Telephone or Cable Outlet	Thickness	0.07 in
Number of Gangs	2	Mounting Type	Exposed Screws
