



Ortronics
TECHCHOICE CAT6A PATCH PANEL, ANGLED 48 PORT
Part No. SPA6AU48



TechChoice Cat6A/ 10G angled 48-port high density patch panel with multiport modules (6 jacks in a group) and utilizes a recessed angle design for a lower mounted profile. Supplied rear cable management. Circuit isolation and supports the alien crosstalk requirements of IEEE 10G and TIA Category 6a cabling specifications. Panel occupies two rack units.

Features & Benefits

Recessed design with lower mounted profile: Directs cords more easily to vertical management.

Tested to TIA 568-C Cat6A with SPC6A cords: More transparent mated union resulting in superior performance.

Universally wired 110 termination: Supports T568A and T568B installs.

Cat6A/10 Gig compatible IDC towers: Designed to accept larger Cat6A cable conductors.

Supplied rear cable management: Supports good cabling practices.

High density design: Maximizes rack utilization.

Specifications

General Info

Product Line	Ortronics	Color	Black
UPC Number	662875996774	Country Of Origin	Mexico
Application Sector	Commercial/Industrial	Type	Panel

Dimensions

Product Width US	19.0 in	Product Depth US	6.09 in
Product Height US	3.5 in		

Additional Information

RoHS Conformant	Yes	Product Environmental Profile	Yes
-----------------	-----	-------------------------------	-----