



Pass and Seymour
FLOOR BOX
Part No. TM1542BOX



Floor Box. 38 cubic inch, with knockouts and Auto/Clamps, three screws for mounting to floor. .

Features & Benefits

Hinged door is removable and easily replaceable.

Standard Decorator opening that accepts GFCI, TVSS, DataCom, or other Decorator devices.

Meets UL514(c) scrub water exclusion test.

Simple mounting box, fits into a 4 3/4 inch hole and mounts with 3 screws included.

UL and cUL Listed.

Made in USA.

Durable construction, impact, and scratch resistant PVC construction.

Auto/Clamps and knockouts on both sides of box.

Threaded device mounting holes.

Ready for low-voltage wiring, drill guides on underside of cover.

Captive screws on TM1542 Series -- screws will not be lost -- new.

Specifications

General Info

Product Line	Pass & Seymour	Country Of Origin	United States
Application Sector	Residential/Commercial	Standard	UL listed

Dimensions

Cubic Capacity	38 cu in
----------------	----------

Listing Agencies / 3rd Party Agencies

cULus Listed	Yes
--------------	-----

Technical Information

Number of Outlets 1
