



radiant Collection
radiant® 15A 4-Way Switch, Black
Part No. TM874BK



For your largest or most open spaces, a radiant® 4-Way Switch enables control of a single light or fixture from three or more separate locations (working in conjunction with 3-Way Switches). Perfect for basements or multi-level rooms. Part of the radiant Collection, it features clean lines and smooth paddle action for a sophisticated touch. Made exclusively for use with screwless Wall Plates from the radiant® Collection, sold separately.

Features & Benefits

Replaces any standard switch with ease, in as little as 10 minutes

Uses a paddle switch for smoother control with a low-profile aesthetic

Features durable, high-impact resistant thermoplastic construction

Designed to install easily with a narrower back body and captivated mounting screws

More color options available to fit any style, including finishes to match current hardware and lighting trends

Complete the look with a sleek, screwless radiant® Wall Plate, and coordinate with other designer switches and outlets available from the radiant® Collection

Specifications

General Info

| | | | |
|--------------------|-------------------------|-------------------------|--------|
| Product Line | Pass & Seymour | Replaced by Part Number | |
| Color | Black | Country Of Origin | Mexico |
| Switch Type | Paddle | Number of Switches | 1 |
| Application Sector | Residential/Commercial | Standard | UL 20 |
| Warranty Type | 1-Year Limited Warranty | | |

Dimensions

| | | | |
|-------------------|---------|------------------|---------|
| Product Width US | 1.43 in | Product Depth US | 1.27 in |
| Product Height US | 4.19 in | | |

Listing Agencies / 3rd Party Agencies

cULus Listed Yes

Additional Information

Product Environmental Profile Yes

Technical Information

| | | | |
|-----------------|---|----------|------|
| Number of Gangs | 1 | Amperage | 15 A |
|-----------------|---|----------|------|

| | | | |
|-----------------|--------------------|---------------|-----|
| Number of Poles | 4-Way, Single Pole | Mounting Type | Box |
|-----------------|--------------------|---------------|-----|

| | |
|---------|-----------|
| Voltage | 120/277 V |
|---------|-----------|
