



radiant Collection
radiant® 15A 4-Way Switch, Nickel
Part No. TM874NICC6



For your largest or most open spaces, a radiant® 4-Way Switch enables control of a single light or fixture from three or more separate locations (working in conjunction with 3-Way Switches). Perfect for basements or multi-level rooms. Part of the radiant Collection, it features clean lines and smooth paddle action for a sophisticated touch. Made exclusively for use with screwless Wall Plates from the radiant® Collection, sold separately.

Features & Benefits

Replaces any standard switch with ease, in as little as 10 minutes

Uses a paddle switch for smoother control with a low-profile aesthetic

Features durable, high-impact resistant thermoplastic construction

Designed to install easily with a narrower back body and captivated mounting screws

More color options available to fit any style, including finishes to match current hardware and lighting trends

Complete the look with a sleek, screwless radiant® Wall Plate, and coordinate with other designer switches and outlets available from the radiant® Collection

Specifications

General Info

Product Line	Pass & Seymour	Replaced by Part Number	
Color	Nickel	Country Of Origin	Mexico
Switch Type	Paddle	Number of Switches	1
Application Sector	Residential	Standard	CSA Listed, UL Listed
Warranty Type	1-Year Limited Warranty		

Dimensions

Product Width US	1.43 in	Product Depth US	1.27 in
Product Height US	4.19 in		

Listing Agencies / 3rd Party Agencies

cULus Listed Yes

Additional Information

Product Environmental Profile Yes

Technical Information

Operating Cycles	50000	Contact Rating	120V
------------------	-------	----------------	------

Number of Gangs	1	Amperage	15 A
-----------------	---	----------	------

Number of Poles	4-Way, Single Pole	Mounting Type	Box
-----------------	--------------------	---------------	-----

Voltage	120/277 V	Environmental Conditions	UL94 V2
---------	-----------	--------------------------	---------
