



Pass and Seymour
15A 125V Fed Spec-Grade Tamper-Resistant USB Type A/A Outlet, Brown
Part No. TR5262USB



Designed for commercial markets with strength and durability in mind, this combination duplex receptacle and two USB Type-A features 3.1A overall USB charging capability and is compatible with USB 2.0 & 3.0 devices. For detailed Tamper-Resistant receptacle information, visit our Tamper-Resistant Receptacles page.

Features & Benefits

- Overall 3.1A USB charging capability: Combination AC duplex receptacles include two 5-volt DC USB ports that work with USB 2.0 & 3.0 compatible devices. Auto-ground clip assures positive ground.
- AC receptacles are tamper-resistant as standard: patented shutter system prevents improper insertion of foreign objects. Multiple color options available.
- Back and side wire terminals accommodate #14 AWG - #10 AWG stranded and solid copper wire. Stainless steel auto-ground clips assure positive ground.
- Wire Size: #14 - #10 AWG Copper Conductor Only

Specifications

General Info

| | | | |
|-----------------------|--|--------------------|-------------------------|
| Product Line | Pass & Seymour | Color | Brown |
| Finish | Matte | Country Of Origin | China |
| Number of Receptacles | 2 | Features | USB-A Charging |
| Outlet Type | Commercial, Indoor, Tamper-Resistant, USB-Charging | Application Sector | Commercial |
| Standard | CSA Listed, cULus, FSUL, UL Listed, RoHS | Warranty Type | 1-Year Limited Warranty |
| Type | Outlet | | |

Dimensions

| | | | |
|------------------|----------|------------------|----------|
| Product Width US | 1.693 in | Product Depth US | 1.392 in |
|------------------|----------|------------------|----------|

| | |
|-------------------|----------|
| Product Height US | 2.677 in |
|-------------------|----------|

Listing Agencies / 3rd Party Agencies

| | |
|--------------|-----|
| cULus Listed | Yes |
|--------------|-----|

Additional Information

| | |
|-------------------------------|-----|
| Product Environmental Profile | Yes |
|-------------------------------|-----|

Technical Information

| | | | |
|---------------------|--------------------------|---------------------|-----|
| Dielectric Strength | Withstands 2000V minimum | Is Tamper-Resistant | Yes |
|---------------------|--------------------------|---------------------|-----|

| | | | |
|--------------|-------|----------------|---|
| USB Amperage | 3.1 A | Number of USBs | 2 |
|--------------|-------|----------------|---|

| | | | |
|------------------|------|--------------------|--------------|
| USB Power Output | 15 W | Temperature Rating | -40° - 60° C |
|------------------|------|--------------------|--------------|

| | | | |
|----------|------|-----------------|-------------|
| Amperage | 15 A | Number of Poles | Double Pole |
|----------|------|-----------------|-------------|

| | | | |
|-----------|-------------|----------------|--------|
| Wire Size | 14 - 10 AWG | Indoor/Outdoor | Indoor |
|-----------|-------------|----------------|--------|

| | |
|---------|---------|
| Voltage | 125.0 V |
|---------|---------|
