



Pass and Seymour
15A 125V Fed Spec-Grade Tamper-Resistant USB Type A/A Outlet, Light Almond
Part No. TR5262USBLA



Designed for commercial markets with strength and durability in mind, this combination duplex receptacle and two USB Type-A features 3.1A overall USB charging capability and is compatible with USB 2.0 & 3.0 devices. For detailed Tamper-Resistant receptacle information, visit our Tamper-Resistant Receptacles page.

Features & Benefits

- Overall 3.1A USB charging capability: Combination AC duplex receptacles include two 5-volt DC USB ports that work with USB 2.0 & 3.0 compatible devices. Auto-ground clip assures positive ground.
 - AC receptacles are tamper-resistant as standard: patented shutter system prevents improper insertion of foreign objects. Multiple color options available.
 - Back and side wire terminals accommodate #14 AWG - #10 AWG stranded and solid copper wire. Stainless steel auto-ground clips assure positive ground.
- Wire Size: #14 - #10 AWG Copper Conductor Only

Specifications

General Info

Product Line	Pass & Seymour	Color	Light Almond
Country Of Origin	China	Number of Receptacles	2
Features	USB-A Charging	Outlet Type	Commercial, Indoor, Tamper-Resistant, USB-Charging
Application Sector	Commercial	Standard	CSA Listed, cULus, FSUL, UL Listed, RoHS
Warranty Type	1-Year Limited Warranty	Type	Outlet

Dimensions

Product Width US	1.693 in	Product Depth US	1.392 in
------------------	----------	------------------	----------

Product Height US	2.677 in
-------------------	----------

Listing Agencies / 3rd Party Agencies

cULus Listed	Yes
--------------	-----

Additional Information

Product Environmental Profile	Yes
-------------------------------	-----

Technical Information

Dielectric Strength	Withstands 2000V minimum	Is Tamper-Resistant	Yes
---------------------	--------------------------	---------------------	-----

USB Amperage	3.1 A	Phase	Single
--------------	-------	-------	--------

Connection	Side & Back Wired	Number of USBs	2
------------	-------------------	----------------	---

Number of Wires	3	USB Power Output	15 W
-----------------	---	------------------	------

Temperature Rating	-40° - 60° C	Amperage	15 A
--------------------	--------------	----------	------

Number of Poles	Double Pole	Wire Size	14 - 10 AWG
-----------------	-------------	-----------	-------------

Indoor/Outdoor	Indoor	Voltage	125.0 V
----------------	--------	---------	---------

Environmental Conditions	UL94 V2
--------------------------	---------
