

Wide Angle Sensor, Passe Infra, 24volt DC



Features & Benefits

Detection Signature Analysis provides high immunity to RFI and EMI.

Wall mount or ceiling mount.

Digital time delay from 15 seconds to 30 minutes.

LED occupancy detection indicator.

Class 2 low-voltage device.

cULus listed.

For covering patents, see www.legrand.us/patents.

2 coverage patterns to choose from.

Adjustable sensitivity settings.

Dual-element, temperature-compensated pyroelectric sensor.

Compatible with 120VAC or 277VAC, 60 Hz lighting systems.

Positive detection indicator.

5-year warranty.

Specifications

General Info

| | | | |
|--------------------|----------------|-------------------|-----------|
| Product Line | Pass & Seymour | Country Of Origin | China |
| Application Sector | Commercial | Standard | UL Listed |

Listing Agencies / 3rd Party Agencies

| | |
|--------------|-----|
| cULus Listed | Yes |
|--------------|-----|

Technical Information

| | | | |
|-------------|------------|------------------|--------|
| Target Size | 1050 sq ft | Operating Cycles | 100000 |
|-------------|------------|------------------|--------|

| | | | |
|-------------|-----------|------|----------------|
| Sensor Type | Occupancy | Body | Thermoplastic |
| Sensitivity | 50/60 Hz | Load | 120/230/277VAC |
