

Pass and Seymour Weatherproof Stainless Steel Cover

Part No. WP23



Stainless Steel Cover, 2 Gang Blank (Box Mounted), Gasketed

Features & Benefits

Covers comply with 2005 NEC Section 406.8(A) and 406.8(B)(2). Ideal for hard-use and corrosive applications.

Plate is Type 302 Stainless Steel for corrosion resistance.

Aesthetically pleasing.

Specifications

Ger	nera	П	nfo

Product Line	Pass & Seymour	Country Of Origin	United States		
Application Sector	Residential/Commercial	Standard	UL Listed		
Dimensions					
Product Width US	4.56 in	Product Height US	4.5 in		
Listing Agencies / 3rd Party Agencies					
CSA Listed	Yes	CSA File Number	17695		
Technical Informati	on				
Number of Outlets	2				