



Pass and Seymour  
Thermoplastic Weatherproof Covers for Flanged Inlet-Outlet  
Part No. WPG2



Industrial Grade Weatherproof Lift Cover, 2.32-inch Diameter Opening to Accommodate 20A/30A Turnlok®, For Flanged Inlet/Outlet

## Features & Benefits

Unbreakable glass-filled polycarbonate construction to withstand years of job site abuse and harsh environmental exposure.

Molded-in label area (2.8 sq. in.) for pre-printed or handwritten labels for identification of circuits, ratings and other application data.

Covers fit all competitive inlets and outlets.

Covers comply with 2005 NEC Section 406.8(A) and 406.8(B)(2).

WPG1 and WPG2 have lockable bullnose for OSHA locktag/tagout compliance.

Tamper-proof hinge features permanent, locked-in pins for added security.

## Specifications

### General Info

Product Line	Pass & Seymour	Color	Gray
Finish	Matte	Country Of Origin	Mexico
Standard	UL Listed, CSA		

### Dimensions

Product Width US	2.85 in	Product Height US	4.57 in
------------------	---------	-------------------	---------

### Listing Agencies / 3rd Party Agencies

cULus ListingNumber	143222	cULus Listed	Yes
---------------------	--------	--------------	-----

### Technical Information

Amperage	20 A	Number of Outlets	1
----------	------	-------------------	---