



Pass and Seymour
Phenolic Medium Base Lampholder 4-Terminal 250V, White
Part No. 276WH



Medium base, phenolic, one-piece keyless, 4 terminals with Tamper-Resistant-drive screws, fits 3 1/4-inch and 4-inch boxes, with cage neck.

Features & Benefits

Quality Materials.

Durability.

Time-tested design. :

Specifications

General Info

Product Line	Pass & Seymour	Color	White
Country Of Origin	China	Application Sector	Residential/Commercial
Standard	UL listed		

Listing Agencies / 3rd Party Agencies

cULus ListingNumber	1204	cULus Listed	Yes
---------------------	------	--------------	-----

Technical Information

Frequency Rating	660Watt	Voltage	250.0 V
------------------	---------	---------	---------