



## Wattstopper Dual Tech Wall Switch Occupancy Sensor, 120/277V, White Part No. DSW-302-W



The DSW-302 dual technology wall switch sensor turns lights ON and OFF based on occupancy and contains two relays for controlling two independent lighting loads or circuits. It combines the benefits of passive infrared (PIR) and ultrasonic detection technologies for high sensitivity to small and large movements. The DSW-302 replaces existing wall switches and fits a standard decorator wall plate.

### Features & Benefits

High sensitivity and dense coverage for exceptional performance

Two relays for control of two separate lighting loads or circuits

Color-matched lens and low profile for appealing design

120/240/277 VAC and 347 VAC models

Defaults to Manual-ON operation for maximum energy savings

Retrieving data. Wait a few seconds and try to cut or copy again.

### Specifications

#### General Info

Product Line	Wattstopper	Color	White
UPC Number	754182935505	Country Of Origin	China
Features	IR (Infrared), Motion Sensor	Switch Type	Motion Sensor
Application Sector	Commercial		

#### Dimensions

Product Width US	2.0 in	Product Weight US	0.47 lb
Product Volume US	35.02 cu in	Product Depth US	2.99 in
Product Height US	4.8 in		

#### Additional Information

---

RoHS Conformant	Yes	Security	Yes
-----------------	-----	----------	-----

---

### Technical Information

---

Response Frequency	50/60 Hz	Sensor Type	Occupancy
--------------------	----------	-------------	-----------

---

Number of Buttons	2	Amperage	8.3 A
-------------------	---	----------	-------

---

Wattage	1200 W	Mounting Type	Box
---------	--------	---------------	-----

---

Sensing Range	180 degrees, 1050 sq ft	Voltage	120/277 V
---------------	-------------------------	---------	-----------

---

Connection Type	Wired	Load	800W
-----------------	-------	------	------

---