



Wattstopper DLM Low Voltage Shade Motor, 40:1 Gear Ratio

Part No. LMSH-MCA140

The DLM low voltage shade motor in 40:1 gear ratio incorporates wired connection and wireless BLE for control options. The motor has a unique counter balance spring design that allows the shades to use less energy and have quiet operation. It is powered by 24-36VDC from the DLM room controller power supply.



Features & Benefits

DLM shade motors feature a unique counterbalance spring system that allows shades to be manually operated by pulling the shade

Low voltage counterbalanced shade motors are quiet and energy efficient

DLM shade motors have integrated BLE (bluetooth low energy) wireless for system setup using mobile apps

Preconfigured four conductor 36 inch low voltage whip and a wide range of preconfigured cable options allow for easy wiring

Rubber crown and coupler dampen vibration and noise

Component of Digital Lighting Management integrated shade and lighting control system

Specifications

General Info

Product Line	Wattstopper	Color	White
UPC Number	842854000023	Application Sector	Commercial

Dimensions

Product Width US	0.749 in	Product Weight US	1.552 lb
Product Volume US	14.4 cu in	Product Height US	0.749 in
Product Length US	13.0 in		

Listing Agencies / 3rd Party Agencies

cUL Listed	Yes
------------	-----

Additional Information

Product Has Potential to Contribute to LEED Yes

Technical Information

Amperage	250 mA	IP Rating	IP44
Speed	38 RPM	Operating Temperature	32°-120°F
