



## C2G

UPS, Line Interactive, LCD, 3000VA, 120V, 2U, (6) 5-20R & (1) L5-30R, 5-30P Cord  
Part No. LU-3000-RTL



Protect critical hardware in IT closets, data networks, retail, and financial branches through automatic voltage regulation (AVR) to correct voltage irregularities without switching to battery. Multiply the reach and ability of IT staff and caretakers through a single portal, providing visibility and control of power usage and available capacity, simplifying maintenance responsibilities for taxed IT departments.

## Features & Benefits

Ultra Low Transfer Time: Quick transfer of power from AC to battery

Automatic Voltage Regulation (AVR): Corrects voltage irregularities without switching to battery

Pure Sinewave Output: Provides the ideal waveform for the most sensitive equipment

Wide Input Voltage Range: Enables stable wide range application usage

Input Power Factor 0.9: Optimized and ideal efficiency at full load

Programmable Outlet Bank: Power management outlets enable programmable control of load segments to extend battery time to mission critical equipment

Optional Remote Management Control: Provides visibility and control of power usage and availability, both on-site or at a remote unmanned facility

4-Post Rack Mounting Kit: Included for simplified rack mounting

Tower Mounting Option: Includes feet for non-rack applications, enabling the UPS to stand up by providing stability

## Specifications

### General Info

Product Line	TBD	Color	Black
UPC Number	662875017585	Country Of Origin	China
Application Sector	Commercial	Standard	UL 1778
Warranty Type	2-Year	Type	UPS (Uninterruptible Power Supply), Active Device

### Technical Information

---

Rack Units	2 U	Plug Type	5-30P
Wattage	3000 W	Mounting	Horizontal
Number of Outlets	8	Voltage	120.0 V

---