



Pass and Seymour
Pin & Sleeve Watertight 60A 3ØY 120V/208V Connector
Part No. PS560C9W



Four pole, Five wire, Pin and Sleeve Connector. 60 amp, 3Y, 120/208 volt.

Features & Benefits

All P&S Watertight Pin & Sleeve plugs, connectors, receptacles, and inlets bring you the features to enhance versatility, reliability, and safety.

And all feature chemical-resistant thermoplastic construction.

An exclusive, hinged cord grip eliminates loose parts that get lost.

North American products come completely ready to wire, for quick, simple installation.

Shrouded, nickel-plated, solid-brass pins provide corrosion protection and excellent conductivity.

For covering patents, see www.legrand.us/patents.

Specifications

General Info

| | | | |
|-------------------|----------------|--------------------|------------|
| Product Line | Pass & Seymour | Color | Gray |
| Country Of Origin | United States | Application Sector | Commercial |
| Standard | UL Listed | | |

Dimensions

| | | | |
|-------------------|---------|-------------------|--------|
| Product Width US | 4.5 in | Product Height US | 4.7 in |
| Product Length US | 10.9 in | | |

Listing Agencies / 3rd Party Agencies

| | | | |
|---------------------|--------|--------------|-----|
| cULus ListingNumber | 151347 | cULus Listed | Yes |
|---------------------|--------|--------------|-----|

Technical Information

| | | | |
|-----------------|---------|-----------|-------|
| Number of Wires | 5 | Amperage | 60 A |
| Number of Poles | 4-Way | Wire Size | 2 AWG |
| Voltage | 120.0 V | | |
