



radiant Collection  
radiant® 15A Tamper-Resistant Ultra-Fast USB Type C/C Outlet, White  
Part No. R26USBCC6WCCV6



Charge phones, tablets and more up to 40% faster, with Ultra-Fast USB Outlets from the radiant® Collection. With an industry-leading 30W of power supplying its two included USB Type-C connections, this outlet helps you get that full battery feeling with convenience and speed – no bulky adapters needed. Easily replacing traditional outlets in as little as ten minutes, the Ultra-Fast updates your space with advanced functionality and the sleek, clean lines of radiant for a sophisticated look. Made exclusively for use with screwless Wall Plates from the radiant® Collection, sold separately.

## Features & Benefits

Provides fast and convenient built-in charging, without sacrificing plugs or requiring a bulky adapter.

Accommodates the latest mobile devices with two USB Type-C connections.

Protects children with a patented tamper-resistant shutter system that prevents improper insertion of foreign objects, complete with "invisi-shutters" for an invisible effect.

More color options available to fit any style, including finishes to match current hardware and lighting trends.

Features an industry-leading 6.0A of power, as well as Smart Chip technology, to maximize charging speed for each USB connection.

All Legrand USB Outlets are manufactured through high-quality design, sourcing and production, and backed by a Lifetime Warranty.

Replaces a traditional outlet easily, in as little as 10 minutes, with features like scalloped cover design and posted side-wire terminal screws for faster installation.

Complete the look with a sleek, screwless radiant® Wall Plate, and coordinate with other designer switches and outlets available from the radiant® Collection.

## Specifications

### General Info

Product Line	Pass & Seymour	Replaced by Part Number	
Color	White	Finish	Matte
Country Of Origin	China	Number of Receptacles	2
Features	USB-C Charging	Outlet Type	Indoor, Residential, Tamper-Resistant, USB-Charging
Warranty Type	1-Year Limited Warranty	Type	Outlet

---

## Dimensions

---

Product Width US	1.693 in	Product Depth US	1.35 in
Product Height US	4.18 in		

---

## Listing Agencies / 3rd Party Agencies

---

cULus Listed	Yes
--------------	-----

---

## Technical Information

---

Is Tamper-Resistant	Yes	USB Amperage	6 A
Number of USBs	2	USB Power Output	15 W
Amperage	15 A	Number of Poles	Double Pole
Indoor/Outdoor	Indoor	NEMA Configuration Code	5-15R
Mounting Type	Box	Voltage	125.0 V
Environmental Conditions	95% (relative humidity, non-condensing)		

---