



Ortronics

**Discontinued - Huawei 02311MNM Compatible 100GBase-PSM4 QSFP28 Transceiver (SMF, 1310nm, 2km, MPO/MTP, DDM, C-Temp)**  
Part No. 02311MNM-L

Huawei 02311MNM Compatible 100GBase-PSM4 QSFP28 Transceiver (SMF, 1310nm, 2km, MPO/MTP, DDM, C-Temp)



## Features & Benefits

**Guaranteed Compatible:** In System tested in over 90 OEM switches, routers and servers.

**99.98% Reliability Rate:** Functionally, optically and environmentally tested to exact specifications.

**Industry Leading Lifetime Warranty:** For more information by product line, visit our Warranty page.

**98% On-Time Delivery Rate:** Extensive inventory guarantees same day shipping.

**Full Service Technical Support:** Call, chat, email or meet for expert optical connectivity support.

## Specifications

### General Info

Product Line	Ortronics	UPC Number	662875064046
Country Of Origin	China	Warranty Type	Lifetime
Type	Transceiver		

### Dimensions

Product Width US	18.35 mm	Product Depth US	119.9 mm
Product Height US	8.5 mm		

### Technical Information

Fiber Optic Cable Type	Single-Mode	Max Distance Support	2 km
Operating Temperature Min	0 °C	Operating Temperature Max	70 °C
Connector Type	MPO	Form Factor	QSFP28