



Pass and Seymour  
20A Single Pole, Double Throw Switch, Brown  
Part No. 1225

Single-Pole, Double-Throw Switch, 20A, 120/277V



## Features & Benefits

Oversize silver alloy contacts for long life and better heat dissipation.	Side wired terminals accept #14 - #10 AWG copper or copper-clad conductors.
Fiber terminal insulation barriers standard.	Can be mounted in standard device boxes or in NEMA 1 sheet steel enclosures.
Bodies, covers, and toggles molded of durable nylon.	Single Pole-Double Throw only.
Locking Switches supplied with one 1498-NT key.	Normally open.
For covering patents, see <a href="https://www.legrand.us/patents">https://www.legrand.us/patents</a> .	For compatible wall plate options, from our TradeMaster unbreakable plates to our radiant screwless plates to our metal wall plates, visit <a href="https://www.legrand.us/electrical-wiring-devices/wall-plates">www.legrand.us/electrical-wiring-devices/wall-plates</a> .

## Specifications

### General Info

Product Line	Pass & Seymour	Color	Brown
Country Of Origin	Mexico	Standard	UL Listed

### Dimensions

Product Width US	1.5 in	Product Depth US	1.469 in
Product Height US	3.281 in		

### Listing Agencies / 3rd Party Agencies

CSA Listed	Yes	cULus Listed	Yes
CSA File Number	17949		
Technical Information			
Amperage	20 A	Wattage	1 W
Voltage	120.0 V		