



Pass and Seymour
20A Single Pole, Double Throw Switch, Gray
Part No. 1225GRY

Single-Pole, Double-Throw Switch, 20A, 120/277V



Features & Benefits

| | |
|---|--|
| Oversize silver alloy contacts for long life and better heat dissipation. | Side wired terminals accept #14 - #10 AWG copper or copper-clad conductors. |
| Fiber terminal insulation barriers standard. | Can be mounted in standard device boxes or in NEMA 1 sheet steel enclosures. |
| Bodies, covers, and toggles molded of durable nylon. | Single Pole-Double Throw only. |
| Locking Switches supplied with one 1498-NT key. | Normally open. |
| For covering patents, see https://www.legrand.us/patents . | For compatible wall plate options, from our TradeMaster unbreakable plates to our radiant screwless plates to our metal wall plates, visit www.legrand.us/electrical-wiring-devices/wall-plates . |

Specifications

General Info

| | | | |
|-------------------|----------------|----------|-----------|
| Product Line | Pass & Seymour | Color | Gray |
| Country Of Origin | Mexico | Standard | UL Listed |

Dimensions

| | | | |
|-------------------|----------|------------------|----------|
| Product Width US | 1.5 in | Product Depth US | 1.469 in |
| Product Height US | 3.281 in | | |

Listing Agencies / 3rd Party Agencies

| | | | |
|------------|-----|--------------|-----|
| CSA Listed | Yes | cULus Listed | Yes |
|------------|-----|--------------|-----|

Technical Information

| | | | |
|----------|------|---------|-----|
| Amperage | 20 A | Wattage | 3 W |
|----------|------|---------|-----|

| | | | |
|---------|---------|--|--|
| Voltage | 120.0 V | | |
|---------|---------|--|--|