



Pass and Seymour
Locking 20A Single Pole, Double Throw Switch
Part No. 1225L

Manual Controller Single-Pole, Double-Throw Switch, 20A, 120/277V, Locking.



Features & Benefits

Oversize silver alloy contacts for long life and better heat dissipation.

Side wired terminals accept #14 - #10 AWG copper or copper-clad conductors.

Fiber terminal insulation barriers standard.

Can be mounted in standard device boxes or in NEMA 1 sheet steel enclosures.

Bodies, covers, and toggles molded of durable nylon.

Single Pole-Double Throw only.

Locking Switches supplied with one 1498-NT key.

Normally open.

For covering patents, see <https://www.legrand.us/patents>.

For compatible wall plate options, from our TradeMaster unbreakable plates to our radiant screwless plates to our metal wall plates, visit www.legrand.us/electrical-wiring-devices/wall-plates.

Specifications

General Info

Product Line	Pass & Seymour	Color	Gray
Finish	Matte	UPC Number	785007122527
Country Of Origin	Mexico	Application Sector	Commercial, Residential
Standard	UL Listed	Type	Manual Controller

Dimensions

Product Width US	1.5 in	Product Depth US	1.469 in
------------------	--------	------------------	----------

Product Height US	3.281 in
-------------------	----------

Listing Agencies / 3rd Party Agencies

CSA Listed	Yes	cULus Listed	Yes
------------	-----	--------------	-----

CSA File Number	17949
-----------------	-------

Technical Information

Amperage	20 A	Number of Poles	Single Pole
----------	------	-----------------	-------------

Wire Size	#14 - #10 AWG
-----------	---------------