




Pass and Seymour  
15A Single Pole, Double Throw Switch, Brown  
Part No. 1250



Single-Pole, Double-Throw Switch. 15A, 120/277VAC rating. Tested to 3 Amps, 24Vdc rating.

## Features & Benefits

Oversize silver alloy contacts for long life and better heat dissipation.

Side wired terminals accept #14 - #10 AWG copper or copper-clad conductors.

Fiber terminal insulation barriers standard.

Can be mounted in standard device boxes or in NEMA 1 sheet steel enclosures.

Bodies, covers, and toggles molded of durable nylon.

Single Pole-Double Throw and Double Pole-Double Throw.

Locking Switches supplied with one 1498-NT key.

Normally open.

For covering patents, see [www.legrand.us/patents](http://www.legrand.us/patents).

For compatible wall plate options, from our TradeMaster unbreakable plates to our radiant screwless plates to our metal wall plates, [click here](#).

## Specifications

### General Info

Product Line	Pass & Seymour	Color	Brown
Country Of Origin	Mexico	Standard	UL Listed

### Dimensions

Product Width US	1.5 in	Product Depth US	1.469 in
Product Height US	3.281 in		

### Listing Agencies / 3rd Party Agencies

CSA Listed	Yes	cULus Listed	Yes
CSA File Number	17949		
Technical Information			
Amperage	15 A	Wattage	1 W
Voltage	120.0 V		