



Pass and Seymour
15A Single Pole, Double Throw Switch, Gray
Part No. 1250GRY



Single-Pole, Double-Throw Switch. 15A, 120/277VAC rating. Tested to 3 Amps, 24Vdc rating.

Features & Benefits

Oversize silver alloy contacts for long life and better heat dissipation.

Side wired terminals accept #14 - #10 AWG copper or copper-clad conductors.

Fiber terminal insulation barriers standard.

Can be mounted in standard device boxes or in NEMA 1 sheet steel enclosures.

Bodies, covers, and toggles molded of durable nylon.

Single Pole-Double Throw and Double Pole-Double Throw.

Locking Switches supplied with one 1498-NT key.

Normally open.

For covering patents, see www.legrand.us/patents.

For compatible wall plate options, from our TradeMaster unbreakable plates to our radiant screwless plates to our metal wall plates, [click here](#).

Specifications

General Info

| | | | |
|-------------------|----------------|----------|-----------|
| Product Line | Pass & Seymour | Color | Gray |
| Country Of Origin | Mexico | Standard | UL Listed |

Dimensions

| | | | |
|-------------------|----------|------------------|----------|
| Product Width US | 1.5 in | Product Depth US | 1.469 in |
| Product Height US | 3.281 in | | |

Listing Agencies / 3rd Party Agencies

| | | | |
|-----------------------|---------|--------------|-----|
| CSA Listed | Yes | cULus Listed | Yes |
| CSA File Number | 17949 | | |
| Technical Information | | | |
| Amperage | 15 A | Wattage | 1 W |
| Voltage | 120.0 V | | |