

Straight Blade Rubber Plug 15amp 250volt 6-15p



Features & Benefits

Rubber body construction stands up to impacts, oils, chemicals, heat, and weather.

Floating blades allow self-alignment with contacts for a firm, even electrical connection.

Terminal screws backed-out, ready-to-wire, saving time and money.

Nickel-plated blades and contacts for long-lasting, superior corrosion resistance.

Quick-drive assembly screws allow for fast installation, saving time and money.

Self-centering cord clamps provide superior strain relief.

For covering patents, see www.legrand.us/patents.

Specifications

General Info

Product Line	Pass & Seymour	Color	Yellow
Country Of Origin	United States	Application Sector	Residential/Commercial
Standard	UL498	Type	Plug Tail

Dimensions

Product Width US	1.53 in	Product Length US	2.27 in
------------------	---------	-------------------	---------

Listing Agencies / 3rd Party Agencies

CSA Listed	Yes	CSA File Number	701645
------------	-----	-----------------	--------

Technical Information

Phase	3	Number of Wires	3
Amperage	15 A	Number of Poles	Double Pole
Wire Size	18 AWG	Voltage	125.0 V
