

Straight Blade Rubber Connector 20amp 125volt 5-20r



Features & Benefits

Rubber body construction stands up to impacts, oils, chemicals, heat, and weather.

Floating blades allow self-alignment with contacts for a firm, even electrical connection.

Terminal screws backed-out, ready-to-wire, saving time and money.

Nickel-plated blades and contacts for long-lasting, superior corrosion resistance.

Quick-drive assembly screws allow for fast installation, saving time and money.

Self-centering cord clamps provide superior strain relief.

For covering patents, see www.legrand.us/patents.

Specifications

General Info

Product Line	Pass & Seymour	Color	Yellow
Country Of Origin	United States	Application Sector	Commercial
Standard	UL 498		

Dimensions

Product Width US	1.93 in	Product Height US	3.74 in
------------------	---------	-------------------	---------

Technical Information

Number of Wires	3	Amperage	20 A
Number of Poles	Double Pole	Wire Size	14 - 10 AWG
Voltage	125.0 V		

