



Pass and Seymour
Discontinued - Portable GFCI Right Angle Plug, Manual
Part No. 1594CMM



Portable Ground Fault Circuit Interrupter, Right Angle Plug, 15amp
125volt, Manual Reset

Features & Benefits

Right angle portable GFCI interrupter

Specifications

General Info

Product Line	Pass & Seymour	Replaced by Part Number	1597CMM
Country Of Origin	China	Application Sector	Commercial
Standard	UL 943/498		

Technical Information

Frequency Rating	60 Hz	Trip Range	5±1 mA
Connection	60Hz	Amperage	15 A
Number of Poles	Double Pole	Voltage	125.0 V