



Pass and Seymour
Discontinued - In-Line Portable 15A GFCI, Manual Reset
Part No. 1594TC2M

Portable Ground Fault Circuit Interrupter, 15amp 125volt, 2' Tri-Cord Connector, Manual Reset



Features & Benefits

In-line portable GFCI interrupter

Specifications

General Info

Product Line	Pass & Seymour	Replaced by Part Number	1597TC2M
Country Of Origin	China	Application Sector	Commercial
Standard	UL 943/498		

Technical Information

Frequency Rating	60 Hz	Trip Range	5±1 mA
Connection	60Hz	Amperage	15 A
Number of Poles	Double Pole	Voltage	125.0 V