



Pass and Seymour

Hospital Grade Isolated Ground Tamper-Resistant 15A Duplex Self-Test GFCI Receptacles with SafeLock® Protection, Orange

Part No. 1597IGHGTRO



Hospital-Grade Isolated Ground Tamper-Resistant 15A Self-Test Duplex GFCI

## Features & Benefits

Hospital Grade Tamper Resistant GFCI

## Specifications

### General Info

Product Line	Pass & Seymour	Color	Orange
Country Of Origin	China	Application Sector	Residential/Commercial
Standard	cULus, UL Listed, FSUL		

### Dimensions

Product Width US	1.73 in	Product Depth US	1.03 in
Product Height US	4.2 in		

### Listing Agencies / 3rd Party Agencies

cULus Listed	Yes
--------------	-----

### Additional Information

Product Environmental Profile	Yes
-------------------------------	-----

### Technical Information

Is Tamper-Resistant	Yes	Interrupt Rating	4 A
Frequency Rating	60 Hz	Trip Range	5±1 mA
Connection	Back and Side Wire	Amperage	15 A
Number of Poles	Double Pole	Voltage	125.0 V

---

Environmental Conditions

95% Humidity, UL 94 V2

---