



Adding weather resistance to ground fault protection, this outlet was designed for use on patios, pool areas, and other outdoor living spaces. Like all GFCI outlets from the radiant® Collection, it self-tests automatically every three seconds to ensure reliable protection from shock due to ground fault occurrences, and makes it easier to recognize and fix trips right where they happen – no more running to the breaker box. Maximize safety, in style, with GFCI protection featuring the sleek, clean lines of radiant. GFCI protection is required by code in bathrooms, kitchens, garages, basements, outdoor areas, and for any other outlets found within six feet of a sink or water source. GFCI outlets should always be used when replacing existing GFCI outlets during renovation. Made exclusively for use with screwless Wall Plates from the radiant® Collection, sold separately.

Features & Benefits

- Protects against shock caused by ground-fault occurrences. Unlike breaker alternatives, GFCI outlets make it easier to fix trips with a convenient reset button on the outlet

Equipped with proven SafeLock protection feature: if critical components are damaged and protection is lost, power to the outlet is disconnected

Designed with weather-resistance for use in outdoor locations such as decks, patios and pool areas. *Must be installed in weatherproof enclosure per NEC requirements

More color options available to fit any style, including finishes to match current hardware and lighting trends

NAFTA-Compliant devices are ideal for use on projects subject to the provisions of the Buy America Act
- Conducts an industry-leading automatic self-test every 3 seconds. If the device ever fails, the indicator light flashes to signal it should be replaced

Extends GFCI protection to "downstream" outlets when used with feed-thru wiring configuration. Note: Will cut power to face and downstream outlets if wired incorrectly

Protects children with a patented tamper-resistant shutter system that prevents improper insertion of foreign objects, complete with "invisi-shutters" for an invisible effect

Complete the look with a sleek, screwless radiant® Wall Plate, and coordinate with other designer switches and outlets available from the radiant® Collection

Specifications

General Info

Product Line	Pass & Seymour	Color	Ivory
Country Of Origin	Mexico	Number of Receptacles	2
Outlet Type	GFCI, Indoor, Self-Test, Tamper-Resistant	Application Sector	Residential/Commercial
Standard	cULus, UL Listed, FSUL	Warranty Type	1-Year Limited Warranty

Dimensions

Product Width US	1.73 in	Product Depth US	1.03 in
Product Height US	4.2 in		

Listing Agencies / 3rd Party Agencies

cULus Listed	Yes
--------------	-----

Additional Information

Product Environmental Profile	Yes
-------------------------------	-----

Technical Information

Interrupt Rating	4 A	Frequency Rating	60 Hz
Trip Range	5±1 mA	Connection	Back and Side Wire
Number of Gangs	1	Amperage	15 A
Mounting Type	Box	Voltage	125.0 V
Environmental Conditions	95% Humidity, UL 94 V2		