



Adjustable Dual Equipment Rack, 84''H x 20.19''W x 21.00'' - 32.00''D, 45RU, 1000 lb. load rating, black.

Features & Benefits

Self-supporting and self-squaring base	Assembles quickly and easily
Top angles and patented reinforced base are standard	Depth adjusts in 1/2''' increments
Mounting holes are roll threaded for 12-24 hardware	Allows excellent cable management opportunities
Constructed of 6061-T6 structural grade aluminum	Equipped with standard 1/2''' junctioning holes for securing multiple-rack lineups
Meets EIA-310 standards	Mounts 19''' equipment and includes cross-recessed black panel mounting screws
Listed to the UL 1863 Standard for Communication Circuit Accessories	Static Load Capacity of 1000 lbs.

Specifications

General Info			
Product Line	Ortronics	UPC Number	662875682516
Country Of Origin	United States	Application Sector	Commercial
Type	Rack		
Dimensions			
Product Width US	20.24 in	Product Depth US	44.0 in
Product Height US	84.0 in		

Additional Information

RoHS Compliant	Yes
----------------	-----
