



Wiremold

CabinetMate Plug-In Outlet Center Unit / 120V/20A/20 long/8 O/L /6' cord/Twist Lock Plug

Part No. 2008ULBC20R-TL



Eight 20A outlets with t-slots, 6' (1.8m) cord. Length 20" (508mm). Receptacle center-to-center 1 1/4" (32mm). 2- Amp unit with a 20A resettable circuit breaker. Units available with straight blade or Locking Plug.

Features & Benefits

Eight 20A outlets with t-slots, 6' (1.8m) cord. Length 20" (508mm). Receptacle center-to-center 1 1/4" (32mm). 2- Amp unit with a 20A resettable circuit breaker. Units available with straight blade or Locking Plug.

Specifications

General Info

| | | | |
|-----------------------|---|--------------------|--------------|
| Product Line | Wiremold | UPC Number | 786776120578 |
| Country Of Origin | Mexico | Receptacle Type | Simplex |
| Number of Receptacles | 8 | Application Sector | Commercial |
| Standard | cULus Recognized: File E66421 Guide XBYS XUHT VZCA | Type | PIOC |

Dimensions

| | | | |
|------------------|--------|-------------------|---------|
| Product Width US | 1.5 in | Product Length US | 20.0 in |
|------------------|--------|-------------------|---------|

Listing Agencies / 3rd Party Agencies

| | | | |
|---------------------|--------|--------------|-----|
| cULus ListingNumber | E66421 | cULus Listed | Yes |
|---------------------|--------|--------------|-----|

Buy American Act Compliance

| | |
|-------|-----|
| NAFTA | Yes |
|-------|-----|

Additional Information

RoHS Conformant Yes

Technical Information

Phase Single Frequency Rating 60 Hz

Amperage 20 A Enclosure Type Aluminum

Mounting Type Spring Clip Voltage 125.0 V

Environmental Conditions Dry interior locations
