



Features & Benefits

Hospital Grade GFCI self-test

Specifications

General Info

| | | | |
|--------------------|------------------------|-------------------------|------------------------|
| Product Line | Pass & Seymour | Replaced by Part Number | PT2097HGNTLTRGRY |
| Color | Gray | Country Of Origin | China |
| Application Sector | Residential/Commercial | Standard | cULus, UL Listed, FSUL |

Listing Agencies / 3rd Party Agencies

| | |
|--------------|-----|
| cULus Listed | Yes |
|--------------|-----|

Technical Information

| | | | |
|------------------|---------|--------------------------|------------------------|
| Interrupt Rating | 4 A | Frequency Rating | 60 Hz |
| Trip Range | 5±1 mA | Connection | Back and Side Wire |
| Amperage | 20 A | Number of Poles | Double Pole |
| Voltage | 125.0 V | Environmental Conditions | 95% Humidity, UL 94 V2 |