



Hospital-Grade Tamper-Resistant 20A Self-Test Duplex GFCI

Features & Benefits

Hospital Grade GFCI self-test

One-piece, brass, triple-wipe power contacts for lasting retention.

Specifications

General Info

| | | | |
|-----------------------|------------------------|-------------------|---|
| Product Line | Pass & Seymour | Color | White |
| Finish | Matte | Country Of Origin | China |
| Number of Receptacles | 2 | Outlet Type | Commercial, GFCI, Indoor, Self-Test, Tamper-Resistant |
| Application Sector | Residential/Commercial | Standard | cULus, UL Listed, FSUL |
| Type | Outlet | | |

Dimensions

| | | | |
|-------------------|---------|------------------|---------|
| Product Width US | 1.73 in | Product Depth US | 1.03 in |
| Product Height US | 4.2 in | | |

Listing Agencies / 3rd Party Agencies

| | |
|--------------|-----|
| cULus Listed | Yes |
|--------------|-----|

Additional Information

| | |
|-------------------------------|-----|
| Product Environmental Profile | Yes |
|-------------------------------|-----|

Technical Information

| | | | |
|------------------|-----|------------------|-------|
| Interrupt Rating | 4 A | Frequency Rating | 60 Hz |
|------------------|-----|------------------|-------|

| | | | |
|-----------------|-------------|----------------|--------|
| Trip Range | 5±1 mA | Amperage | 20 A |
| Number of Poles | Double Pole | Indoor/Outdoor | Indoor |
| Voltage | 125.0 V | | |