



Pass and Seymour  
Hospital Grade Tamper-Resistant Weather-Resistant 20A Duplex Self-Test GFCI Receptacles with SafeLock® Protection, Light Almond  
Part No. 2097HGTRWRLA



Hospital-Grade Tamper-Resistant Weather-Resistant 15A Self-Test Duplex GFCI

Features & Benefits

Hospital Grade GFCI self-test

CH versions feature a factory broken split circuit tab allowing you to control half of the receptacle.

Specifications

General Info

|                   |  |                       |              |
|-------------------|--|-----------------------|--------------|
| Product Line      | Pass & Seymour   | Color                 | Light Almond |
| Country Of Origin | China  | Number of Receptacles | 2            |
| Outlet Type       | Commercial, GFCI, Outdoor, Tamper-Resistant, Weather-Resistant | Type                  | Outlet       |

Dimensions

|                   |         |                  |         |
|-------------------|---------|------------------|---------|
| Product Width US  | 1.73 in | Product Depth US | 1.13 in |
| Product Height US | 4.2 in  |                  |         |

Listing Agencies / 3rd Party Agencies

|              |     |
|--------------|-----|
| cULus Listed | Yes |
|--------------|-----|

Technical Information

|                |         |                 |             |
|----------------|---------|-----------------|-------------|
| Amperage       | 20 A    | Number of Poles | Double Pole |
| Indoor/Outdoor | Outdoor | Voltage         | 125.0 V     |