

Locking Rubber Plug 15amp 125volt L5-15p



## Features & Benefits

Rubber body construction stands up to impacts, oil, chemicals, heat, and weather.

Neoprene grommet keeps out contaminants at cord entrance.

Nickel-plated blades and connectors provide an extra measure of corrosion resistance.

Multiple seals between plug and connector on watertight version protects electrical connection from contaminants.

Floating blades allow self-alignment with contacts and reduce stress on blades and contacts.

Terminal screws come backed out -- ready-to-wire.

Closure cap on watertight model forms a seal to keep out contaminants when connector is not in use.

## Specifications

### General Info

Product Line	Pass & Seymour	Color	Yellow
Country Of Origin	United States	Application Sector	Industrial
Standard	UL498	Type	Plug Tail

### Dimensions

Product Width US	1.6 in	Product Length US	2.44 in
------------------	--------	-------------------	---------

### Listing Agencies / 3rd Party Agencies

CSA Listed	Yes	CSA File Number	701645
------------	-----	-----------------	--------

### Technical Information

Number of Wires	3	Amperage	15 A
Number of Poles	Double Pole	Wire Size	14 - 10 AWG
Voltage	125.0 V		