



Wiremold
25DTC-E10 - 25DTC Series Blank Steel Tele-Power Express Pole
Part No. 25DTC-E10



25DTC Series 10' Blank Express (2-piece) Poles in Ivory gives you all of the benefits of our standard 25dtp poles, with better shipping and easier handling. The unique 2-piece design ships in a 6 foot carton, and is easy to assemble, allowing the pole to be shipped quickly to your job site. It can handle all of your needs effortlessly, whether it's power, data, or A/V wiring you need to bring down to the desk, workstation, or cash registers, while being aesthetically pleasing with multiple color options. The vertical drop poles give you the flexibility and capacity to devote both sides of the pole for single service or separate the two channels to provide dual service feeds. This pole comes with two(2) prewired Fed-Spec general grade duplex receptacles, 20A 125V. Knockouts provided in removable cover for RJ11/RJ45 and modular furniture communication connectors. All mounting hardware, entrance end plate, and two ceiling trim plates are included.

Features & Benefits

Two sections of a two-compartment pole (5'4" (1.626m) base + 5' (1.524m) extender) assemblies to form a 10' 4" (3.148m) pole. Nominal material thickness .040" (1.0mm). Ivory or gray boot base. Furnished unwired without outlets. Mounting hardware, entrance end plate and ceiling trim plate furnished. An 8" (203mm) cover at top front of pole is removable for making power wiring connections.

Dual-channel. Allows a single drop point for access to multiple services.

Multiple color options. Available in four aesthetic colors: white, black, ivory, and gray.

Pole extenders combine quick installation with easy job-site handling. Snap together 5' sections to create a pole or extend the length of your existing 25TP series pole. These new extenders accommodate a variety of ceiling heights, can ship UPS or air freight for quick & reliable delivery.

Relocatable. Ready for service in 30 minutes or less. Can be quickly reconfigured or relocated as work space uses and service needs change.

Wide selection of standard options. Stocked in a variety of materials, finishes, and heights.

Datacom connectivity options. Accepts industry standard and proprietary devices from a wide range of manufacturers to provide a seamless, aesthetically pleasing interface for voice, data, audio, and video applications at the point of use.

Custom capabilities. Modify receptacle type and location, change color finish, alter pole heights, add fixture whips and more.

Specifications

General Info

Product Line	Wiremold	UPC Number	786776172553
--------------	----------	------------	--------------

Country Of Origin	United States	Standard	cULus Listed Multioutlet Assemblies: File E15191 E178348 Guide PVGT, Raceway Fittings: File E41751 Guide RJPR, Accessories: File E53857 Guide RVUR Meets Article 380 & 386 of NEC
-------------------	---------------	----------	--

Dimensions

Product Width US	2.312 in	Product Height US	125.98 in
------------------	----------	-------------------	-----------

Listing Agencies / 3rd Party Agencies

cULus ListingNumber	E15191	cULus Listed	Yes
---------------------	--------	--------------	-----

Buy American Act Compliance

NAFTA	Yes
-------	-----

Additional Information

RoHS Conformant	Yes
-----------------	-----