



Wiremold
25DTP-E10 - 25DTP Series Steel Tele-Power Pole (Ivory)
Part No. 25DTP-E10



Two sections of a two-compartment (power and communication) pole (5'4" (1.626m) base + 5' (1.524m) extender) assembles to form a 10' 4" (3.148m) pole. Nominal material thickness .040" (1.0mm). Ivory or gray boot base. Factory wired with fed-spec general grade 20A 125V duplex style receptacles. An 8" (203mm) cover at top front (power side) of pole is removable for making power wiring connections. KOs provided in removable cover for RJ11/RJ45 and modular furniture communication connectors. Mounting hardware, entrance end plate and two ceiling trim plates furnished.

Features & Benefits

Add power receptacles or devices to existing modular Tele-Power Poles. Includes one receptacle mounting bracket. Face diameter of single receptacle: 1.38" -1.40" (35mm - 36mm).

Specifications

General Info

Product Line	Wiremold	UPC Number	786776172539
Country Of Origin	United States	Standard	cULus Listed Multioutlet Assemblies: File E15191 E178348 Guide PVGT, Raceway Fittings: File E41751 Guide RJPR, Accessories: File E53857 Guide RVUR Meets Article 380 & 386 of NEC

Dimensions

Product Width US	2.83 in	Product Height US	125.0 in
------------------	---------	-------------------	----------

Listing Agencies / 3rd Party Agencies

cULus ListingNumber	E15191	cULus Listed	Yes
---------------------	--------	--------------	-----

Additional Information

RoHS Conformant	Yes
-----------------	-----