Pass and Seymour
Specification Grade Decorator Switch, White
Part No. 2603347W

Specification Grade Decorator Switch 3-way, Back and Side-Wire, Canadian Decorator Switch, 15A, 347V

Features & Benefits

Impact-resistant polycarb back body and frame.

Cushioned thermoplastic paddle assures smooth, quiet, long term operation.

Unique single rocking butterfly contact provides long term consistent performance with significantly fewer moving parts.

Internal screw-pressure-plate back and side wire capability for easy installation with #14 - #10 stranded or solid copper/copper clad wire.

Terminals made of high conductivity brass and serrated for maximum wire gripping.

Silver alloy contacts integrally formed to the butterfly actuator assures reliable performance.

Integral auto-ground clip for positive ground to metal boxes.

Tri-drive ground, terminal, and mounting screws.

All terminal screws backed out, ready-to-install.

For covering patents, see

Specifications

General Info

Product Line	Pass & Seymour	Color	White
Country Of Origin	Mexico	Application Sector	Industrial
Standard	UL 20		

Dimensions

Product Width US	1.3 in	Product Depth US	1.06 in
Product Height US	4.2 in		

Listing Agencies / 3rd Party Agencies

CSA Listed	Yes	cULus Listed	Yes
CSA File Number	17446		

Technical Information

Contact Rating	15amp, 347vac	Amperage	15 A
Wattage	3 W	Voltage	347.0 V