



Pass and Seymour  
Trademaster® 15A/125V Duplex Receptacle, Ivory  
Part No. 3232I



Our Pass and Seymour TradeMaster® receptacles combine a traditional look with reliable, time-tested operation for any residential application.

## Features & Benefits

Durable, high-quality construction

125-volt outlet

Wire Size: #12 - #14 AWG, Solid wire

## Specifications

### General Info

Product Line	Pass & Seymour	Color	Ivory
Finish	Matte	Country Of Origin	China
Number of Receptacles	2	Outlet Type	Commercial, Indoor, Residential
Application Sector	Residential/Commercial	Standard	UL 498
Type	Outlet		

### Dimensions

Product Width US	1.32 in	Product Depth US	0.96 in
Product Height US	4.2 in		

### Listing Agencies / 3rd Party Agencies

cULus ListingNumber	140596	cULus Listed	Yes
---------------------	--------	--------------	-----

---

Additional Information

---

Product Environmental Profile    Yes

---

Technical Information

---

Amperage	15 A	Number of Poles	Double Pole
Wire Size	14 - 12 AWG	Indoor/Outdoor	Indoor
Voltage	125 V		

---