



Pass and Seymour  
Trademaster® 15A 125V Self-Grounding Duplex Receptacle, Brown  
Part No. 3232S



15A/125A Trademaster® Duplex Receptacle

## Features & Benefits

Quality Materials, durability, and time-tested design

## Specifications

### General Info

Product Line	Pass & Seymour	Color	Brown
Finish	Matte	Country Of Origin	China
Number of Receptacles	2	Outlet Type	Commercial, Indoor, Residential, Self-Grounding
Application Sector	Residential	Standard	UL498, CSA C22.2 No. 42
Type	Outlet		

### Dimensions

Product Width US	1.32 in	Product Depth US	0.96 in
Product Height US	3.31 in		

### Listing Agencies / 3rd Party Agencies

cULus ListingNumber	140596	cULus Listed	Yes
---------------------	--------	--------------	-----

---

Additional Information

---

Product Environmental Profile	Yes
-------------------------------	-----

---

Technical Information

---

Temperature Rating	-30° - 60° C	Amperage	15 A
Number of Poles	Double Pole	Wire Size	14 - 12 AWG
Indoor/Outdoor	Indoor	Voltage	125.0 V

---