



Pass and Seymour
Trademaster® 15A 125V Self-Grounding Tamper-Resistant Duplex Receptacle, Brown
Part No. 3232TRS



15A/125A Trademaster® Self-Grounding, Tamper-Resistant Duplex Receptacle

Features & Benefits

Quality Materials, durability, and time-tested design	Two drive screws anchor strap to back body and face where abrupt removal torque is greatest.
---	--

Specifications

General Info

Product Line	Pass & Seymour	Color	Brown
Country Of Origin	China	Number of Receptacles	2
Outlet Type	Commercial, Indoor, Residential, Self-Grounding, Tamper-Resistant	Application Sector	Residential
Standard	cULus UL498, CSA C22.2 No. 42	Type	Outlet

Dimensions

Product Width US	1.32 in	Product Depth US	1.0 in
Product Height US	3.31 in		

Listing Agencies / 3rd Party Agencies

cULus Listed	Yes
--------------	-----

Additional Information

Product Environmental Profile Yes

Technical Information

Is Tamper-Resistant	Yes	Connection	push wire, Side wire
Number of Wires	3	Temperature Rating	-30° - 60° C
Amperage	15 A	Number of Poles	Double Pole
Wire Size	14 - 12 AWG	Indoor/Outdoor	Indoor
Voltage	125 V	Environmental Conditions	Flammability: UL94 V2