



Wiremold
Discontinued - Power Commander PDU/120V/30A/single phase/24 pcs 5-20R O/L
Part No. 3A44B2-1



Two 15A resettable circuit breakers. Twenty-four 20A outlets with T-slots, gray housing. 12' (3.6m) cord. Length 48" (1.3m).

Specifications

General Info

Product Line	Wiremold	UPC Number	786776034370
Country Of Origin	Mexico	Receptacle Type	Simplex
Number of Receptacles	24	Application Sector	Commercial
Standard	cULus Listed: File E173292 Guide NWGQ	Type	PIOC

Listing Agencies / 3rd Party Agencies

cULus ListingNumber	E173292	cULus Listed	Yes
---------------------	---------	--------------	-----

Buy American Act Compliance

NAFTA	Yes
-------	-----

Additional Information

RoHS Conformant	Yes
-----------------	-----

Technical Information

Phase	Single	Frequency Rating	60 Hz
-------	--------	------------------	-------

Amperage	20 A	Enclosure Type	Aluminum
Mounting Type	Z Bracket, Swivel Bracket, Drop-In Clip, Spring Clip, L Bracket	Voltage	100.0 V
Environmental Conditions	Dry interior locations		
