



Weatherproof Heavy Cast Aluminum Cover Decorator/Ground Fault Circuit Interrupter Horizontal

Features & Benefits

- Extremely durable for hard-use institutional applications.
- Die-cast copper-free aluminum construction.
- Screws and spring covers are chrome-plated brass.
- Heavy rubber gaskets provide positive seal.
- Comply with 2005 NEC Section 406.8(A) and 406.8(B)(2).
- Spring-loaded covers close automatically when plugs are removed.
- Stainless steel springs.
- Baked-on lacquer finish.
- All covers below are for 4 screw mounting only.

Specifications

General Info

Product Line	Pass & Seymour	Color	Gray
Finish	Satin	UPC Number	785007451108
Country Of Origin	China	Wall Plate Type	Custom
Application Sector	Commercial, Industrial	Standard	UL Listed
Warranty Type	1-Year Limited Warranty	Type	Weatherproof Cast Cover

Dimensions

Product Width US	5.25 in	Product Depth US	0.125 in
Product Height US	4.27 in		

Listing Agencies / 3rd Party Agencies

CSA Listed	Yes	CSA File Number	16807
------------	-----	-----------------	-------

Technical Information

Number of Gangs	1	Indoor/Outdoor	Indoor
Mounting Type	Box Mounted	Orientation	Horizontal
Number of Outlets	1		